

HERO

(SL73N)

The Hero goes with you wherever you go and can be assembled or disassembled in just seconds. The Hero is super light and compact, and can be stored in small areas such as the trunk or back seat of your car. The compact features support easy transportation of your Hero for today's active lifestyle. The Hero can be used in confined spaces both indoors and out.

Available Colors



Blue



Red



Overall Dimensions (L' x W x H)	in	37 x 20 x 36
Number, Size of Tires (front; rear)	Front (rear)	1, 8" (2, 8")
Suggested User Weight (on a level road)	lb	250
Weight of Heaviest Part (w/o batteries, baskets and seat)	lb	35
Total Weight (w/ batteries, basket, seat)	lb	70
Each Battery Module Weight	lb	15
Battery Module Capacity	_V_Ah x Pcs	12V10Ah x 2
Charger		Off Board (2A)
Output Power of Motor	hp	0.45
Maximum Speed ²	mph	3.8
Max. Climbing Angle/Safe Climbing Angle (based on user weight of 90kg/200lb.)	% (°)	15 (9) 130lbs/10 (6) 187 lbs
Range (per charge) (After the battery and mechanical moving parts fully break in)	mile	8
Turning Radius	in	32
Handle Bar	Type	T-Bar
Drive Wheel	Type	Rear Wheel

All specifications are subject to change without prior notice. Shoprider Mobility Products, Inc. reserves the rights of any changes to the unit.

1) Include the anti-tip wheel or the rear castor.

2) Driver weight may exceed weight of the unit; speed must be reduced when turning.

3) The actual driving range varies with the factors shown as below:

a) The weight of occupant

b) Ground surface

c) Battery capacity and conditions

d) Type of charger

e) Ambient temperature

f) The way of driving

g) If the battery and mechanical

moving parts fully break in

h) Etc.

- **250 lbs. weight capacity**
- **Quick Connect battery pack**
- **Charge battery pack at any convenient location on/off the scooter**
- **Puncture proof tires**
- **Adjustable seat height**



Optional Fitted Bag in the Seat available



Optional back cushion w/pouch, Armrest available

SHOPRIDER

Toll-Free: 800.743.0772

www.shoprider.com