

FULL SIZE PORTABLE SCOOTER



Seat Color
Black Vinyl

Body Colors
Blue
Red

Ride

LiteRider^{GOLDEN}
4 wheel

Enjoy the best of both worlds with the LiteRider™ 4-wheel scooter! The LiteRider is a full-size scooter with all of the benefits of a compact, portable scooter! The LiteRider comes standard with a Delta Tiller and a large, 17" x 16" stadium style seat with adjustable armrests. With a 300 lb. weight capacity, the LiteRider can be quickly and wirelessly disassembled for transport or storage.



Model	GL140
Medicare Code	K0800
Weight Capacity	300 lbs
Drive Wheels	Rear
Maximum Speed	5 mph
Operating Range ¹	9.5 miles
Ground Clearance to center deck	3.75"
Ground Clearance to transaxle/motor	2.5"
Turning Radius	48"
Type Batteries	2-18AH
Colors	Red, Blue
Freewheel Mode	Yes
Electronic Speed Control	Yes
Electro-Mechanical Brakes	Yes
Charger	Off Board
Controller	90 Amp Dynamic R Series
Dimensions	
Length	43.25"
Width	22"
Height (ground to top of back of seat)	37" - 39"
Ground to Top of Seat	23.5" - 25.5"
Ground to Top of Deck	6"
Deck to Top of Seat	18" - 20"
Number of Seat Height Adjustments	3
Size of Increments	1"
Front Axle to Rear Axle	30"
Weight of Unit: (assembled)	129 lbs
Front Half	52 lbs
Rear Half	28 lbs
Seat w/Arms	22 lbs
Batteries	25 lbs/pack
Tires:	Solid/Low Profile
Front	9"
Rear	9"
Rear Anti-Tippers	2"
Standard Seat	Stadium Style
Back Height - no headrest	16"
Width x Depth	17" X 16"
Color	Black Vinyl
Warranty:	
Frame	Lifetime
Drive Train	2 Years
Electronics ²	2 Years

¹. Battery range will vary due to rider weight, drive surface and terrain.

². Electronics warranty excludes batteries.

Features

- Delta Tiller standard
- 300 lb. weight capacity
- Rugged anti-rust steel frame tubing
- Rugged plastic floor mat for optimum durability
- Disassembles quickly and easily

Enjoy quick and wireless disassembly!



Pick up the seat



Pull out the battery pack



Remove the baskets from under the seat and from the tiller (not shown)



To separate the rear transaxle from the frame, squeeze the release lever located on the underside of the frame



While squeezing the release lever, pull up on the rear frame



Red



Blue



Disassembles into six pieces for transport and storage! No wires to connect or disconnect!

Literature is current at time of printing. Golden Technologies reserves the right to make changes to the product or literature at any time.