

XtraLite 3 & 4

(TE-787NA-UL3)
(TE-787NA-UL4)

The XtraLite 3 scooter allows you to move through small spaces with ease and stability. Just like the XtraLite 3, the XtraLite 4 is affordable and comes with full features. With its patented quick connect battery pack, charging your scooter has never been so easy. Dirt easily falls through the wire mesh cover. This four-wheel scooter allows you to drive around with stability and style.



XtraLite 3



XtraLite 4

		XtraLite 3	XtraLite 4
Overall Dimensions (L' x W x H)	in	45 x 21 x 37	41 x 20 x 35
Number, Size of Tires (front; rear)	Front (rear)	1, 8" (2, 8")	2, 7" (2, 8")
Suggested User Weight (on a level road)	lb	Max. 250	Max. 250
Weight of Heaviest Part (w/o baskets and seat)	lb	44	53
Total Weight (w/ batteries, basket, seat)	lb	79	89
Each Battery Module Weight	lb	22	22
Battery Module Capacity	_V_Ah x Pcs	12V12Ah x 2	12V12Ah x 2
Charger		Off Board (2A)	Off Board (2A)
Output Power of Motor	hp	0.47	0.45
Maximum Speed ²	mph	3.75	3.75
Max. Climbing Angle/Safe Climbing Angle (based on user weight of 90kg/200lb.))	% (°)	10 (6)/17 (10)	10 (6)/17(10)
Range (per charge) (After the battery and mechanical moving parts fully break in)	mile	11	10
Turning Radius	in	39	46
Ground Clearance	in	3	3
Handle Bar	Type	T-Bar	T-Bar
Drive Wheel	Type	Front Wheel	Rear Wheel

- **250 lbs. weight capacity**
- **Quick Connect battery pack**
- **Charge battery pack at any convenient location on/off the scooter**
- **Puncture proof tires**
- **2 convenient baskets**
- **Adjustable arm rests**
- **Adjustable wheelbase width for increased stability (XtraLite 3 Only)**

All specifications are subject to change without prior notice. Shoprider Mobility Products, Inc. reserves the rights of any changes to the unit.

1) Include the anti-tip wheel or the rear castor.

2) Driver weight may exceed weight of the unit; speed must be reduced when turning.

3) The actual driving range varies with the factors shown as below:

a) The weight of occupant

b) Ground surface

c) Battery capacity and conditions

d) Type of charger

e) Ambient temperature

f) The way of driving

g) If the battery and mechanical

moving parts fully break in

h) Etc.

SHOPRIDER

Toll-Free: 800.743.0772

www.shoprider.com